

# uvex

## SAFETY EYEWEAR


25.04.2019

### Product Datasheet model u-sonic 9308 147



**UVEX ARBEITSSCHUTZ GMBH, Würzburger Str. 181-189,  
D-90766 Fürth**

<b>Product characteristics</b>	<ul style="list-style-type: none"><li>• small, compact low weight goggle</li><li>• compatible with other PPE</li><li>• ergonomic design with soft flexible components – adapts to any facial shape</li><li>• high mechanical strength (B: 120 m/s)</li><li>• low pressure, wide fully adjustable head strap for excellent wearer comfort</li><li>• indirect ventilation system helps maintain a comfortable climate around the eyes</li><li>• Suitable for Oil &amp; Gas applications</li></ul>
<b>Technical details</b>	
<b>Frame</b>	<b>Front piece</b>
Material	PP / TPE
Colour	black, grey

Material	<b>Headband</b>
Features	synthetic headband
Colour	individually adjustable grey, black
Manufacturer's ID code	<b>Marking</b> W
Applicable EN norm	166
Field of use	3 (drops and splashes of liquid) 4 (large dust particles)
Impact resistance	B (120 m/s)
Conformity symbol	CE
<b>Lens</b>	
Material	PC
Thickness	2,1 mm
Coating	uvex supravision plus
Colour	clear
UV protection	UV 400
Filter	<b>Marking</b> 2C-1,2 (DIN EN 170)
Manufacturer's ID code	W
Optical class	1
Impact resistance	B (120 m/s)
Surface resistance to fine particles	K
Antifog	N
Conformity symbol	CE
Factory symbol	

**Miscellaneous**

Weight	69 g
Packing	5 spectacles per box 90 spectacles per cardboard box
Standards	DIN EN 166 + DIN EN 170
PPE Category	Category II