


Product Datasheet model u-sonic 9308 246

**UVEX ARBEITSSCHUTZ GMBH, Würzburger Str. 181-189,
D-90766 Fürth**

| | |
|--|---|
| Product characteristics | <ul style="list-style-type: none">• small, compact low weight goggle• compatible with other PPE• ergonomic design with soft flexible components – adapts to any facial shape• high mechanical strength (B: 120 m/s)• low pressure, wide fully adjustable head strap for excellent wearer comfort• indirect ventilation system helps maintain a comfortable climate around the eyes• reduced ventilation |
| Technical details Frame Material Colour | Front piece PP / TPE anthracite, yellow |

| | |
|--------------------------------------|---|
| Manufacturer's ID code | Marking W |
| Applicable EN norm | 166 |
| Field of use | 3 (drops and splashes of liquid) 4 (large dust particles) |
| Impact resistance | B (120 m/s) |
| Conformity symbol | CE |
| Material | Headband |
| Features | synthetic headband |
| Colour | individually adjustable anthracite, yellow |
| Lens | |
| Material | PC |
| Thickness | 2,1 mm |
| Coating | uvex supravision extreme |
| Colour | clear |
| UV protection | UV 400 |
| Filter | Marking |
| Manufacturer's ID code | 2C-1,2 (DIN EN 170) W |
| Optical class | 1 |
| Impact resistance | B (120 m/s) |
| Surface resistance to fine particles | K |
| Antifog | N |
| Conformity symbol | CE |
| Factory symbol |  |

Miscellaneous

| | |
|--------------|---|
| Weight | 69 g |
| Packing | 5 spectacles per box 90 spectacles per cardboard box |
| Standards | DIN EN 166 + DIN EN 170 |
| PPE Category | Category II |