


Product Datasheet model u-sonic 9308 247

**UVEX ARBEITSSCHUTZ GMBH, Würzburger Str. 181-189,
D-90766 Fürth**

Product characteristics	<ul style="list-style-type: none">• small, compact low weight goggle• compatible with other PPE• ergonomic design with soft flexible components – adapts to any facial shape• high mechanical strength (B: 120 m/s)• low pressure, wide fully adjustable head strap for excellent wearer comfort• indirect ventilation system helps maintain a comfortable climate around the eyes• reduced ventilation
Technical details	
Frame	Front piece
Material	PP / TPE
Colour	black, red

Material	Headband
Features	synthetic headband
Colour	individually adjustable black, red
Manufacturer's ID code	Marking W
Applicable EN norm	166
Field of use	3 (drops and splashes of liquid) 4 (large dust particles)
Impact resistance	B (120 m/s)
Conformity symbol	CE
Lens	
Material	PC
Thickness	2,1 mm
Coating	uvex supravision excellence
Colour	clear
UV protection	UV 400
Filter	Marking 2C-1,2 (DIN EN 170)
Manufacturer's ID code	W
Optical class	1
Impact resistance	B (120 m/s)
Surface resistance to fine particles	K
Antifog	N
Conformity symbol	CE
Factory symbol	

Miscellaneous

Weight	69 g
Packing	5 spectacles per box 90 spectacles per cardboard box
Standards	DIN EN 166 + DIN EN 170
PPE Category	Category II