

**Product Datasheet model sportstyle 9193 064**

**UVEX ARBEITSSCHUTZ GMBH, Würzburger Str. 181-189,  
D-90766 Fürth**

**Product  
characteristics**

- extremely light safety spectacle with a sporty design
- optimal vision thanks to the shape of the uvex lens, with scratch-resistant coating on the outside and anti-fog coating on the inside
- soft, adjustable nose piece and soft, non-slip ear pieces (uvex duo component technology) ensure a secure, pressure-free fit
- with CBR 65-Lens Technology:
  - C**ontrast (contrast-enhancing)
  - B**lue (reduction of blue light)
  - R**elax (relaxed view)
  - 65** (65% transmission)

## Technical details

### Frame

Material  
Features  
Colour

Material  
Colour

Manufacturer's ID  
code  
Applicable EN norm  
Impact resistance  
Resistance to high  
speed particles at  
extremes of  
temperat.  
Conformity symbol

### Front piece


PC-PBT / TPE  
individually adjustable nose pad  
white

### Temples

PC-PBT / TPE  
white, black

### Marking

W  
  
166  
F (45 m/s)  
T  
  
CE

<b>Lens</b>	
Material	PC
Thickness	2,1 mm
Coating	uvex supravision extreme
Colour	light brown (CBR 65)
UV protection	UV 400
<b>Marking</b>	
Filter	5-1,4 (DIN EN 172)
Manufacturer's ID code	W
Optical class	1
Impact resistance	F (45 m/s)
Resistance to high speed particles at extremes of temperat.	T
Surface resistance to fine particles	K
Antifog	N
Conformity symbol	CE
Factory symbol	
<b>Miscellaneous</b>	
Weight	23 g
Packing	5 spectacles per box 160 spectacles per cardboard box
Standards	DIN EN 166 + DIN EN 172
PPE Category	Category II