


Product Datasheet model ultravision 9301 714

**UVEX ARBEITSSCHUTZ GMBH, Würzburger Str. 181-189,
D-90766 Fürth**

Product characteristics	<ul style="list-style-type: none">• classic goggles with unrestricted field of vision• can be worn over prescription spectacles• lenses can be changed• high mechanical strength of the cellulose acetate lens (F: 45 m/s)• innovative indirect ventilation system helps maintain a comfortable climate around the eyes
Technical details	
Frame	Front piece
Material	PVC
Features	ventilation system
Colour	transparent light grey
Headband	
Material	synthetic headband
Features	adjustable
Colour	anthracite/lime

Manufacturer's ID code	Marking W
Applicable EN norm	166
Field of use	3 (drops and splashes of liquid) 4 (large dust particles)
Impact resistance	F (45 m/s)
Conformity symbol	CE
Lens	
Material	CA
Thickness	1,2 mm
Coating	inside antifog
Colour	clear
UV protection	UV 380
Filter	
Manufacturer's ID code	Marking 2-1,2 (DIN EN 170) W
Optical class	1
Impact resistance	F (45 m/s)
Antifog	N
Conformity symbol	CE
Factory symbol	
Miscellaneous	
Weight	119 g
Packing	80 pieces in one carton
Standards	DIN EN 166 + DIN EN 170
PPE Category	Category II