

Product Datasheet model ultravision 9301 813

**UVEX ARBEITSSCHUTZ GMBH, Würzburger Str. 181-189,
D-90766 Fürth**

Product characteristics

- Anatomical shape and soft material allow close, yet comfortable fit
- Fits comfortably over most prescription spectacles
- Nose bridge works well with respirators
- Frosted top to reduce glare
- High-quality, easily adjustable headband
- Optically correct lens (EN 166 class 1) does not distort view or cause headaches
- 2 tear-off films included
- Simple lens replacement reduces cost


Technical details**Frame**

Material
Features
Colour

Front piece

PVC
ventilation system
transparent light grey

Material	Headband
Features	synthetic headband
Colour	adjustable
	anthracite-lime
	Marking
Manufacturer's ID code	W
Applicable EN norm	166
Field of use	3 (drops and splashes of liquid)
	4 (large dust particles)
Low-energy impact	B (120 m/s)
Resistance to high speed particles at extremes of temperat.	T
Conformity symbol	CE
Lens	
Material	PC
Thickness	2,2 mm
Coating	supravision excellence
Colour	clear
UV protection	UV 400

	Marking
Filter	2C-1,2 (DIN EN 170)
Manufacturer's ID code	W
Optical class	1
Impact resistance	B (120 m/s)
Resistance to high speed particles at extremes of temperat.	T
Surface resistance to fine particles	K
Antifog	N
Conformity symbol	CE
Factory symbol	
Miscellaneous	
Weight	125 g
Packing	90 pieces in one carton
Standards	DIN EN 166 + DIN EN 170
PPE Category	Category II