



Product Datasheet model ultrasonic flip-up 9302 043**UVEX ARBEITSSCHUTZ GMBH, Würzburger Str. 181-189,
D-90766 Fürth****Product
characteristics**

- Panoramic lens shape allows 180° uninterrupted lateral vision
- High degree of mechanical strength
- High level of protection for professional welders
- Integrated, indirect ventilation allows air movement directly across the lens
- Flip-up filter, minimum damage from welding sparks
- Easily replaceable lens filter
- Easy to combine with other PPE products
- New filter technology
- Perfect colour recognition
- UV and IR radiation protection
- High-quality, easily adjustable headband

Technical details	
Frame	
Material	Front piece PP/TPE
Colour	green/black
Manufacturer's ID code	Marking W
Applicable EN norm	166
Field of use	3 (drops and splashes of liquid) 4 (large dust particles)
Impact resistance	B (120 m/s)
Conformity symbol	CE
Material	Headband synthetic headband
Features	individually adjustable
Colour	black/green
flip-up	
Material	PC
Thickness	2,2 mm
Coating	infradur
Colour	grey
UV protection	UV 400
IR protection	fulfilled
Filter	Marking 3 (DIN EN 169)
Manufacturer's ID code	W
Optical class	1
Conformity symbol	CE
Factory symbol	

Lens	
Material	PC
Thickness	2,2 mm
Coating	supravision excellence
Colour	clear
UV protection	UV 400
	Marking
Filter	2-1,2 (DIN EN 170)
Manufacturer's ID code	W
Optical class	1
Impact resistance	B (120 m/s)
Surface resistance to fine particles	K
Antifog	N
Conformity symbol	CE
Factory symbol	
Miscellaneous	
Weight	126 g
Packing	4 goggles per box 72 pieces in one carton
Standards	DIN EN 166, 169, 170
PPE Category	Category II