


Product Datasheet model ultrasonic 9302 601

**UVEX ARBEITSSCHUTZ GMBH, Würzburger Str. 181-189,
D-90766 Fürth**

Product characteristics	<ul style="list-style-type: none">• goggles in sporty design, can also be worn over prescription spectacles• lenses can be changed• high mechanical strength (B: 120 m/s)• wide panoramic field of vision• hard and soft components create soft, pressure free seal for comfortable all day
Technical details	
Frame	
Material	Front piece PP/TPE (flame-retarding)
Colour	black/red
Material	Headband synthetic headband
Features	individually adjustable
Colour	black/red

Manufacturer's ID code	Marking W
Applicable EN norm	166
Field of use	3 (drops and splashes of liquid) 4 (large dust particles)
Impact resistance	B (120 m/s)
Conformity symbol	CE
Lens	
Material	PC
Thickness	2,2 mm
Coating	uvex supravision extreme
Colour	clear
UV protection	UV 400
Filter	Marking 2-1,2 (DIN EN 170)
Manufacturer's ID code	W
Optical class	1
Impact resistance	B (120 m/s)
Surface resistance to fine particles	K
Antifog	N
Conformity symbol	CE
Factory symbol	
Miscellaneous	
Weight	91 g
Packing	4 goggles per box 72 pieces in one carton
Standards	DIN EN 166 + DIN EN 170
PPE Category	Category II