


Product Datasheet model sportstyle 9193 880

**UVEX ARBEITSSCHUTZ GMBH, Würzburger Str. 181-189,
D-90766 Fürth**

Product characteristics	<ul style="list-style-type: none">• extremely light safety spectacle with a sporty design• optimal vision thanks to the shape of the uvex lens• uvex variomatic lenses accommodate fast in changing UV irradiation conditions by automatic darkening (10 s) and lightening (30 s)• soft, adjustable nose piece and soft, non-slip ear pieces (uvex duo component technology) ensure a secure, pressure-free fit
Technical details Frame Material Features Colour	Front piece PC-PBT / TPE individually adjustable nose pad black

Material	Temples
Colour	PC-PBT / TPE black, anthracite
Manufacturer's ID code	Marking W
Applicable EN norm	166
Impact resistance	F (45 m/s)
Resistance to high speed particles at extremes of temperat.	T
Conformity symbol	CE
Lens	
Material	PC
Thickness	2,1 mm
Coating	uvex supervision variomatic
Colour	light green
UV protection	UV 400
Filter	Marking 2-1,2 (DIN EN 170)
Manufacturer's ID code	W
Optical class	1
Impact resistance	F (45 m/s)
Resistance to high speed particles at extremes of temperat.	T
Surface resistance to fine particles	K
Antifog	N
Conformity symbol	CE
Factory symbol	

Miscellaneous

Weight

23 g

Packing

1 spectacle per box

42 spectacles per cardboard box

Standards

DIN EN 166 + DIN EN 170

PPE Category

Category II