

**Product Datasheet model uvex x-fit 9199 005**

**UVEX ARBEITSSCHUTZ GMBH, Würzburger Str. 181-189,  
D-90766 Fürth**

**Product  
characteristics**

- Functional and sporty Design
- Perfect closed fitting
- X-shaped soft nose design for stability and protection
- High-performance uvex supravision coating
- with uvex Comfort-Slider for inclination and optimized fitting
- Temple as duo-component equipment-rail for functional add-ons:
  - easy adaptable and adjustable headband (item. no. 9958 023) for a secure fitting
  - uvex LED mini light for additional lightning (item no. 9999 100)

## Technical details

### Frame

Material  
Colour

Model No.  
Manufacturer's ID  
code  
Applicable EN norm  
Impact resistance  
Resistance to high  
speed particles at  
extremes of temp.  
Conformity symbol

Material  
Colour

### Lens

Material  
Thickness  
Coating  
Colour  
UV protection

### Temples

ABS  
white, anthracite

### Marking


9199  
W  
166  
F (45 m/s)  
T

CE

### Comfort Slider

TPE  
anthracite

PC (Lens)  
TPE (x-Nose)  
1,9 mm  
uvex supravision sapphire  
clear (Lens)  
anthracite (x-Nose)  
UV 400

Filter	<b>Marking</b> 2C-1,2 (DIN EN 170)
Manufacturer's ID code	W
Optical class	1
Impact resistance	F (45 m/s)
Resistance to high speed particles at extremes of temperat.	T
Surface resistance to fine particles	K
Conformity symbol	CE
Factory symbol	
<b>Miscellaneous</b>	
Weight	28 g
Packing	5 spectacles per box 160 spectacles per cardboard box
Standards	DIN EN 166 + DIN EN 170
PPE Category	Category II