

Product Datasheet model uvex x-fit 9199 276

**UVEX ARBEITSSCHUTZ GMBH, Würzburger Str. 181-189,
D-90766 Fürth**

**Product
characteristics**

- Functional and sporty Design
- Perfect closed fitting
- X-shaped soft nose design for stability and protection
- High-performance uvex supravision coating
- with uvex Comfort-Slider for inclination und optimized fitting
- Temple as duo-component equipment-rail for functional add-ons:
 - easy adaptable and adjustable headband (item. no. 9958 023) for a secure fitting
 - uvex LED mini light for additional lightning (item no. 9999 100)

Technical details

Frame

Material
Colour

Temples

ABS
anthracite, light grey

Model No.
Manufacturer's ID
code
Applicable EN norm
Impact resistance
Resistance to high
speed particles at
extremes of temp.
Conformity symbol

Marking

9199
W
166
F (45 m/s)
T
CE

Material
Colour


Comofrt-Slider

TPE
anthracite

Lens

Material
Thickness
Coating
Colour
UV protection

PC (Lens)
TPE (x-Nose)
1,9 mm
uvex supravision excellence
grey 23% (Lens)
anthracite (x-Nose)
UV 400

	Marking
Filter	5-2,5 (DIN EN 172)
Manufacturer's ID code	W
Optical class	1
Impact resistance	F (45 m/s)
Resistance to high speed particles at extremes of temperat.	T
Surface resistance to fine particles	K
Antifog	N
Conformity symbol	CE
Factory symbol	
Miscellaneous	
Weight	28 g
Packing	5 spectacles per box 160 spectacles per cardboard box
Standards	DIN EN 166 + DIN EN 172
PPE Category	Category II