


**Product Datasheet model ultravision 9301 633**

**UVEX ARBEITSSCHUTZ GMBH, Würzburger Str. 181-189,  
D-90766 Fürth**

<b>Product characteristics</b>	<ul style="list-style-type: none"><li>• classic goggles with unrestricted field of vision</li><li>• can be worn over prescription spectacles</li><li>• lenses can be changed</li><li>• high mechanical strength of the polycarbonate lens (B: 120 m/s)</li><li>• gastight version with improved heat resistant frame material</li></ul>
<b>Technical details</b>	
<b>Frame</b>	<b>Front piece</b>
Material	TPU
Features	gastight
Colour	red

Manufacturer's ID code	<b>Marking</b> W
Applicable EN norm	166
Field of use	3 (drops and splashes of liquid) 4 (large dust particles) 5 (gases and fine dust particles)
Impact resistance	B (120 m/s)
Conformity symbol	CE
Material	<b>Headband</b> synthetic headband
Features	adjustable
Colour	black, red
Fixing	PC Headband Closure
<b>Lens</b>	
Material	PC
Thickness	2,2 mm
Coating	uvex supravision excellence
Colour	clear
UV protection	UV 400
Filter	<b>Marking</b> 2C-1,2 (DIN EN 170)
Manufacturer's ID code	W
Optical class	1
Impact resistance	B (120 m/s)
Field of use	9 (molten material and hot solids)
Surface resistance to fine particles	K
Antifog	N
Conformity symbol	CE
Factory symbol	

**Miscellaneous**

Weight	128 g
Packaging	90 pieces in one carton
Standards	DIN EN 166 + 170
PPE Category	Category II