

## Product Datasheet uvex 1 business 8428.1-3 S3 SRC

**UVEX ARBEITSSCHUTZ GmbH, Würzburger Str. 181-189, D-90766 Fürth**

<b>General features</b>	<ul style="list-style-type: none"><li>• Low weight and flexible S3 safety shoe in modern business look</li><li>• Colour accents and details</li><li>• Wide fit</li><li>• breathable high-tech micro velour upper material</li><li>• All sole materials are free of silicones, plasticisers and other paint wetting impairment substances</li></ul>
<b>Protection features</b>	<ul style="list-style-type: none"><li>• Meets ESD requirements: resistance to ground &lt; 35 megaohm</li><li>• Steel toe cap</li><li>• Ergonomically designed outsole made from dual density polyurethane with excellent slip resistance</li><li>• Penetration-resistant, non-metallic midsole in accordance with the latest safety standards, does not restrict flexibility of the shoe</li></ul>
<b>Comfort features</b>	<ul style="list-style-type: none"><li>• Soft padding on collar and dust tongue</li><li>• Removable comfort insole, antistatic, with moisture control system</li><li>• Light weight</li><li>• Outstanding wearer comfort results from optimised last and climate-optimised, breathable materials</li></ul>
<b>Outsole</b>	<ul style="list-style-type: none"><li>• PUR outsole, non-marking</li><li>• Ergonomically designed tread</li><li>• Extremely flexible</li><li>• Resistant to oil and petrol</li></ul>

	<ul style="list-style-type: none"> <li>Resistant to temperatures for short periods up to ca. +120°C</li> <li>Excellent slip resistance</li> </ul>																
<b>Certificates</b>	<ul style="list-style-type: none"> <li>Certified with uvex medicare for individual, orthopaedic inlay soles and individual adjustments of the sole unit such as overall increase, inside and outside increase and other solutions</li> </ul>																
<b>Areas of application</b>	<ul style="list-style-type: none"> <li>Light application</li> </ul>																
<b>Technical data</b>	<table> <tr> <td>Art.-No.</td> <td>8428.1</td> <td>.2</td> <td>.3</td> </tr> <tr> <td>Width</td> <td>10</td> <td>11</td> <td>12</td> </tr> <tr> <td>Standard</td> <td colspan="3">EN ISO 20345:2011 S3 SRC</td> </tr> <tr> <td>Size</td> <td colspan="3">39 – 52</td> </tr> </table>	Art.-No.	8428.1	.2	.3	Width	10	11	12	Standard	EN ISO 20345:2011 S3 SRC			Size	39 – 52		
Art.-No.	8428.1	.2	.3														
Width	10	11	12														
Standard	EN ISO 20345:2011 S3 SRC																
Size	39 – 52																
<b>Accessories</b>	<p><i>Comfortable climatic insole</i> (Article-No.: 9515.7-.9)</p> <ul style="list-style-type: none"> <li>Provides the foot with exceptional, full-surface shock absorption and ensures comfort in high-strain zones</li> <li>Ultra breathable and moisture-absorbing materials</li> <li>Shock absorption zones that assist natural movement</li> <li>Non-irritating, comfortable surface structure</li> </ul> <p><i>Laces</i></p> <ul style="list-style-type: none"> <li>Black (Article-No.: 9599.7.99)</li> </ul>																