

uvex

SAFETY
FOOTWAR
medicare

SBU-OH
PGM-orthopaedics
10.04.2015

Product data sheet uvex motion 3XL 6496.3 S3 SRC ESD



UVEX ARBEITSSCHUTZ GMBH, Würzburger Str. 181-189, D-90766 Fürth

product infomations

- wide-expanded low shoe
- anatomical asymetrical last
- less lining seams to avoid pressure marks
- breathable ; hydrophobing hightech-mikrovelours-uppermaterail
- breathable distance mesh lining material
- suitable for chrome allergic sufferer because all materials are synthetical
- extra wide+expanded uvex medicap toe cap 100% metalfree latest generation ; formed asymetrical ; no thermal conductibility ; unmagnetic
- metalfree insole for penetration resistance fulfills latest standard specification ; prevents cold bridges
- individual adaptable elastic laces
- soft cushioned topline edge
- soft tongue padding
- extended uvex anti-twist counter for more stability and to avoid twisting one's ankle
- individual convertible uvex hydroflex®foam-

	<p>EVA soft foot bed</p> <ul style="list-style-type: none"> -EVA space holder; 6mm conductive; black -enough space for diabetes-adaptic foot bed -fulfills ESD requirements -variable PUR outsole individual orthopedic adaptable up to 3 cm leg length reduction -neutral to vanish surfaces 								
outsole	<ul style="list-style-type: none"> -PUR ESD non-marking outsole -ergonomic profiled -fulfills request of SRC -short-term heat-resistant about +120°C -individual orthopedic adjustable (EVA material thus extra light after adjustment) up to max 3 cm leg length reduction then short-term heat-resistant about +60°C -particulare little PUR weight -permanently flexibel -extended shell-shaped at the toe cap to reduce knock-on effect and extended shell-shaped at the counter for better heel stabilisation -oil- and gasolin-resistant ; resistant to the most chemical products 								
technical data	<table> <tbody> <tr> <td>item number</td> <td>6496.3</td> </tr> <tr> <td>width</td> <td>> 15</td> </tr> <tr> <td>norm</td> <td>EN ISO 20345:2011 S3 SRC</td> </tr> <tr> <td>sice</td> <td>35-50</td> </tr> </tbody> </table>	item number	6496.3	width	> 15	norm	EN ISO 20345:2011 S3 SRC	sice	35-50
item number	6496.3								
width	> 15								
norm	EN ISO 20345:2011 S3 SRC								
sice	35-50								