

Product Datasheet LED head torch 9790.063 KS- UVPHEX



UVEX ARBEITSSCHUTZ GMBH, Würzburger Str. 181-189, D-90766 Fürth

Product features

- KS-UVPHEX with two separate reflective elements for long-distance and flood lighting
- Compact design , developed for the pheos visor system
- explosion-proof version
- ATEX admission
- Four different operating modes
- Protection level IP 67 (dust- and waterproof)
- For use in temperatures ranging from -20 °C to + 60° C
- Light source: 1,7 AH Li-Ion accumulator
- Beam energy up to a maximum of 115 IM
- Beam duration 25 hours

Weight	80 g (without batteries)
Delivery	LED head torch, charging adapter, micro USB charger

Versions

Article number	Colour/Version	Retail unit
9790.062	LED head torch KS-UVPH	1 piece
9790.063	LED head torch KS-UVPHEX (ATEX)	1 piece