



TKHS 315 M - 3,1 WNB

- Restart protection: prevents unintentional start-up after power supply interruption
- Precise, powerful table saw in professional configuration – quick to adapt for every application
- Ideal for sawing squared timber, boards, panels and wood-like materials in the workshop and at construction sites
- Quiet induction motor with motor brake and overload protection - maintenance-free and robust.
- Mitre fence with linear stop, can also be used as a sliding table
- Sturdy rip fence with quick fastening
- Freely height-adjustable saw blade
- Comfortable setting of the saw blade inclination from the front
- Sturdy, powder-coated sheet steel design and galvanised table-top
- Foldable table length extension
- Frame and motor pre-mounted

Order no.	0103153100
EAN code	4003665403403
Dimensions	1700 x 700 x 1000 mm // 5.6 x 2.3 x 3.3 ft
Max. support surface	800 x 600 mm // 31 1/2 x 23 5/8 "
Working height	850 mm // 33 1/2 "
Cutting height	0 - 85 mm // 0 - 3 5/16 "
Maximum cutting height	85 / 53 mm // 3 5/16 / 2 1/16 "
Maximum cutting width at rip fence	340 mm / 13 3/8 "
Maximum material width at mitre fence	250 mm / 9 13/16 "
No-load speed	2990 rpm
Cutting speed	50 m/s / 164 ft/s
Saw blade	315 x 30 mm // 12 3/8 x 1.181 "
Saw blade swivel range	0 - 45 °
Mains voltage	220 - 240 V
Rated input power	3100 W
Weight	75 kg / 165 lbs

Scope of delivery

Carbide saw blade with alternately bevel-ground tips (24 teeth), Wheel set incl. handles, Rip Fence, Mitre Fence, Table extension (600 x 800 mm), Chip and Dust Extraction Unit, Push stick