



PS 7500 S

- For pumping empty, pumping dry and circulating fresh water or dirty water from containers, tanks or flooded cellars
- For garden irrigation from water reservoirs
- Double seal system for protection of the pump if the water is particularly dense or contains large particles
- Overload protection: protects the motor from overheating
- Adjustable float switch for automatic mode
- Robust housing made of impact-proof plastic
- Ergonomic handle for comfortable transport

Order no.	0250750000
EAN code	4003665502274
Rated input power	450 W
Maximum delivery rate	7500 l/h / 1981 gal/h
Maximum delivery height	5 m / 16 ft
Maximum pressure	0.5 bar / 7.3 psi
Maximum immersion depth	5 m / 16.4 ft
Discharge port	1 1/4" female thread
Pump housing	Plastic
Protection type IP	IP X8
Maximum particle size up to	30 mm / 1 3/16 "
Number of impellers	1
Dimensions	257 x 200 x 315 mm // 10 1/8 x 7 7/8 x 12 13/32 "
Weight	4.8 kg / 10.6 lbs
Cable length	10 m / 33 ft

Scope of delivery

Angle connection piece with multi-adapter, Float switch