



TP 7500 SI

- For pumping empty, pumping dry and circulating clear water from containers, tanks, tanks or flooded cellars
- For garden irrigation from water reservoirs
- Overload protection: protects the motor from overheating
- Low-intake level up to a residual water level of 2-3 mm
- Integrated float switch for automatic mode
- Integrated check valve and automatic bleed
- Problem-free use in narrower shafts up to 25 x 25 cm
- Universal port

Order no.	0250750013
EAN code	4003665401546
Rated input power	300 W
Maximum delivery rate	7500 l/h / 1981 gal/h
Maximum delivery height	6.5 m / 21 ft
Maximum pressure	0.65 bar / 9.4 psi
Maximum immersion depth	5 m / 16 ft
Discharge port	1 1/4" Male Thread
Pump housing	Plastic
Protection type IP	IP 68
Maximum particle size up to	5 mm / 3/16 "
Number of impellers	1
Dimensions	227 x 185 x 285 mm // 8 15/16 x 7 9/32 x 11 7/32 "
Weight	4.2 kg / 9.3 lbs
Cable length	10 m / 33 ft

Scope of delivery

Multi-adapter