



TDP 7501 S

- For garden irrigation from water reservoirs
- For directly operating irrigation systems as well as for watering and garden irrigation using bore water, wells or cisterns
- For garden irrigation with 1 to 3 sprinklers
- 3-level pump gearing provides optimum pressure build-up
- Overload protection: protects the motor from overheating
- Adjustable float switch for automatic mode
- Integrated non-return valve reliably prevents the water pipe from running dry
- Robust housing made of impact-proof plastic
- Ergonomic handle for comfortable transport

Order no.	0250750100
EAN code	4003665502281
Rated input power	1000 W
Maximum delivery rate	7500 l/h / 1981 gal/h
Maximum delivery height	34 m / 112 ft
Maximum pressure	3.4 bar / 49.3 psi
Maximum immersion depth	7 m / 23 ft
Discharge port	1" female thread
Pump housing	Plastic
Protection type IP	IP X8
Maximum particle size up to	0 mm
Number of impellers	3
Dimensions	150 x 150 x 380 mm // 5 29/32 x 5 29/32 x 14 31/32 "
Weight	9.1 kg / 20.1 lbs
Cable length	10 m / 33 ft

Scope of delivery

Multi-adapter, Float switch