



## TP 12000 SI

- For pumping empty, pumping dry and circulating clear water from containers, tanks, tanks or flooded cellars
- For garden irrigation from water reservoirs
- Overload protection: protects the motor from overheating
- Low-intake level up to a residual water level of 2-3 mm
- Integrated float switch for automatic mode
- Integrated check valve and automatic bleed
- Problem-free use in narrower shafts up to 25 x 25 cm
- Universal port

Order no.	025120009
EAN code	4003665401553
Rated input power	600 W
Maximum delivery rate	11700 l/h / 3091 gal/h
Maximum delivery height	9 m / 30 ft
Maximum pressure	0.9 bar / 13.1 psi
Maximum immersion depth	7 m / 23 ft
Discharge port	1 1/4" Male Thread
Pump housing	Plastic
Protection type IP	IP 68
Maximum particle size up to	5 mm / 3/16 "
Number of impellers	1
Dimensions	230 x 190 x 320 mm // 9 1/16 x 7 1/2 x 12 19/32 "
Weight	5.1 kg / 11.2 lbs
Cable length	10 m / 33 ft

### Scope of delivery

Multi-adapter