



## FSR 200 Intec

- Light and handy machine for convenient one-handed operation
- Very good weight/performance ratio, ideal for working overhead
- Grip area with non-slip soft-grip surface
- Dust-proof ball bearings for long service life of the machine
- Robust clamping system for sanding paper with or without hook and loop fastener
- Dust cartridge with filter for working without connecting to a vacuum cleaner
- Extraction possibility by means of connecting to an all-purpose vacuum cleaner via an adapter (accessory)

| Order no.<br>EAN code          | 600066500<br>4007430153128 |
|--------------------------------|----------------------------|
| Base plate                     | 114 x 102 mm (1/4 sheet)   |
| Rated input power              | 200 W                      |
| No-load speed                  | 13000 rpm                  |
| Orbital frequency with no load | 26000 opm                  |
| Orbit diameter                 | 1.4 mm / 1/16 "            |
| Weight (without power cable)   | 1.3 kg / 2.9 lbs           |
| Cable length                   | 2.8 m / 9 ft               |

### Scope of delivery

Hole Punch, Dust collection cartridge, 1 Pleated filter, Plastic carry case