



SXE 425 TurboTec

- Variospeed (V) Electronics for working at customised speeds to suit various application materials
- Thumbwheel for speed preselection
- Turbo boost: allows additional power reserves to be employed for maximum removal
- Power Control System: No scratches when placing the machine directly onto the material at speed
- Grip area with non-slip soft-grip surface
- Removable side handle
- Dust-proof ball bearings for long service life of the machine
- Sturdy aluminium die cast bearing housing
- Easy to empty textile dust bag for working without extraction facilities
- Extraction possibility by means of connecting an all-purpose vacuum cleaner
- Multi-hole sanding pad for effective extraction and a longer service life of the sanding medium

Order no.	600131000
EAN code	4007430164315
Diameter of backing pad	125 mm / 5 "
Rated input power	320 W
No-load speed	4200 - 11000 rpm
Orbital frequency with no load	8400 - 22000 rpm
Orbit diameter	5 mm / 3/16 "
Weight (without power cable)	2 kg / 5.1 lbs
Cable length	4 m / 13 ft

Scope of delivery

Sanding pad "multi-hole" with hook and loop, Hexagonal wrench, removable side handle, Textile dust bags