



LSV 5-225 Comfort with Variable Length Adjustment

- For convenient sanding of primed surfaces on walls or ceilings
- Selectable LED side light to help detect imperfections and serrations and ensure a perfect finish.
- Optimum balance when working, as the centre of gravity of the machine is not at the sanding head
- Variable length adjustment: can be shortened or extended without tools for narrow rooms or high ceiling rooms
- Extendable to a total length of 2.1 m with additional extension (accessory)
- M-Clean technology: Effective extraction through the machine housing for maximum flexibility of the sanding head
- Ideal adaptation of the flexible sanding head to the surface for good work results
- Optimum extraction results thanks to spring-mounted brush rim that adapts to the surface.
- Vario-Constamatic (VC)-Full wave electronics for working at customised speeds to suit the application materials, and speeds that remain almost constant even under load
- Ergonomically shaped aluminium handle bar and T-handle for comfortable use in different positions
- Simple, quick and tool-free exchangeable shaft can be adjusted directly on site if needed
- Putting the machine down without kinking the hose and cable
- With extensive range of grinding media for every application
- Extraction possibility by means of connecting an all-purpose vacuum cleaner

Order no.	600136000
EAN code	4007430282675
Sanding disc diameter	225 mm / 8 7/8 "
No-load speed	1000 - 1650 rpm
Rated input power	500 W
Output power	270 W
Adjustable machine length	1.1 / 1.6 / 2.1 m // 41 3/8 / 61 7/32 / 81 1/16 "
Weight (without power cable)	4.5 kg / 9.9 lbs
Cable length	4 m / 157 1/2 "

Scope of delivery

Sanding pad (very soft), Hook and loop sanding sheets with multi-perforation (1 each of P80, P100, P120, P150), Flexible shaft (as replacement), Coupling bush, Extension, Hexagonal wrench, Plastic carry case