



BF 18 LTX 90

- Powerful, compact cordless band file for grinding, burnishing and deburring in places difficult to reach
- Robust motor for long service life
- Tool-free change of sanding belt and adjustable belt guide
- Grinding attachment can be swivelled by 270° without tools for perfect adaptation to any working position
- Battery pack can be swivelled for better working in hard to reach places
- Detachable dust filter protects motor from coarse particles
- Overload protection: protects the motor from overheating
- Electronic soft start for smooth start-up
- Restart protection: prevents unintentional start-up after battery pack change
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	600321850
EAN code	4007430207005
Battery voltage	18 V
Belt speed in idle	8 m/s // 1575 ft/min
Grinding belt width	6 - 19 mm // 1/4 - 3/4 "
Grinding belt length	457 mm / 18 "
Useful length of sanding belt arm	90 mm / 3 9/16 "
Weight without battery pack	2.1 kg / 4.6 lbs
Weight with battery pack	2.5 kg / 5.5 lbs

Scope of delivery

Side handle, Dust protection filter, Sanding belt arm 1 (for belt width 6 and 13 mm), Hexagonal wrench, without battery pack, without charger