



W 9-125 Quick with quick-locking nut

- Low fatigue as never before: compact angle grinder with smallest handle circumference in its class for perfect ergonomics
- Longer service life, more power: the Metabo Marathon-motor with patented dust protection, up to 20% more overload capacity and 50% more torque
- Tool free, fast disc change at the touch of a button with the Metabo M-Quick-System
- Tool-free adjustable guard; twist-proof
- Metabo S-automatic mechanical safety clutch: minimises kick-back to the lowest level when the disc jams unexpectedly - for maximum user safety and swift progress
- Restart protection after power interruption
- Gear housing can be unscrewed, rotated in 90° steps and re-mounted for left-handed operation or cutting
- Auto-stop carbon brushes to protect the motor

Order no.	600374000
EAN code	4007430240989
Disc-Ø	125 mm // 5 "
Rated input power	900 W
Output power	550 W
No-load speed	10500 rpm
Speed at rated load	7500 rpm
Torque	2.5 Nm / 22 in-lbs
Spindle thread	M 14
Handle circumference	193 mm / 7.5594 "
Weight (without power cable)	2.1 kg / 4.6 lbs
Cable length	4 m / 13 ft

Scope of delivery

Guard, Inner support flange, M-Quick flange nut, Side handle