



SRE 3185

- Lightweight, handy sander with perfect ergonomics
- Excellent sanding finish without scoring marks and grooves, for a professional surface finish
- Grip area with non-slip soft-grip surface
- Low-vibration working thanks to smooth running operation
- Robust aluminium die cast bearing flange
- Robust clamping system for sanding paper with or without hook and loop fastener
- Vario (V)-Electronics for working at customised orbital frequencies to suit various application materials
- Easy to empty textile dust bag for working without extraction facilities
- Extraction possibility by means of connecting an all-purpose vacuum cleaner

Order no. EAN code	600442000 4007430271129
Base plate	92 x 184 mm (1/3 sheet)
Rated input power	210 W
No-load speed	11200 rpm
Orbital frequency with no load	8800 - 22300 rpm
Orbit diameter	2 mm / 1/16 "
Weight (without power cable)	1.5 kg / 3.3 lbs
Cable length	4 m / 13 ft

Scope of delivery
Textile dust bags