



## GEP 710 Plus

- Paddle switch with deadmans function: safe to operate due to an ergonomically integrated non-slip switch
- Long grinding spindle - ideal for working on hard to reach places
- Spindle lock for simple change of tools
- Aluminium die-cast bearing flange for long service life of the machine
- Vario-Constamatic (VC)- Electronics for work with materials requiring customised speeds, which remain almost constant under load
- Thumbwheel for Speed Preselection
- Electronic safety shutdown of the motor for safe working in case the tool stops unexpectedly
- Restart protection: prevents unintentional start-up after power supply interruption
- Electronic overload protection for long service life
- Precise collar for stationary use
- Removable protective rubber cap for comfortable and safe working
- Slim design for ideal handling
- Precision collet for precise concentricity
- Metabo Marathon motor with patented dust protection for long service life

Order no.	600617000
EAN code	4007430213532
No-load speed	10000 - 30500 rpm
Rated input power	710 W
Output power	430 W
Speed at rated load	24000 rpm
Collar diameter	43 mm / 1 11/16 "
Collet chuck bore	6 mm / 0.2362 "
Weight (without power cable)	1.6 kg / 3.5 lbs
Cable length	4 m / 13 ft

### Scope of delivery

Collet 6 mm, Protective rubber cap, 1 Open-jawed spanner