



## BE 650

- Small, handy drill
- Vario (V)-Electronics for working at customised speeds to suit various application materials
- Thumbwheel for speed preselection
- Forward and reverse rotation
- Spindle with hexagonal recess for screwdriver bits for working without chuck
- Handle with non-slip soft-grip surface

Order no.	600741000
EAN code	4061792201620
Rated input power	650 W
Output power	320 W
Drill Ø steel	13 mm // 1/2 "
Drill-Ø soft wood	30 mm // 1 3/16 "
Speed at rated load	1500 rpm
Gears	1
Collar diameter	43 mm / 1 11/16 "
Chuck capacity	1.5 - 13 mm // 1/16 - 1/2 "
Drill spindle with hexagonal recess	6.35 mm / 1/4 "
Drill spindle thread	1/2 " - 20 UNF
Weight (without power cable)	1.8 kg
Cable length	2.5 m / 8 ft

### Scope of delivery

Geared chuck, Chuck key