



## SBE 650

- Vario (V)-Electronics for working at customised speeds to suit various application materials
- Thumbwheel for Speed Preselection
- Forward and reverse rotation
- Spindle with hexagonal recess for screwdriver bits for working without chuck

Order no.	600742850
EAN code	4061792201484
Rated input power	650 W
Output power	320 W
Maximum torque	10 Nm // 88 in-lbs
Drill-Ø masonry	16 mm / 5/8 "
Drill-Ø concrete	14 mm / 9/16 "
Drill Ø steel	13 mm // 1/2 "
Drill-Ø soft wood	30 mm // 1 3/16 "
Speed at rated load	1500 rpm
Maximum impact rate	44800 bpm
Gears	1
Chuck capacity	1.5 - 13 mm // 1/16 - 1/2 "
Collar diameter	43 mm / 1 11/16 "
Drill spindle with hexagonal recess	6.35 mm / 1/4 "
Drill spindle thread	1/2 " - 20 UNF
Chuck clamping type	Keyless chuck
Weight (without power cable)	1.8 kg
Cable length	2.5 m / 8 ft

### Scope of delivery

Futuro Plus keyless chuck, Side handle, Drilling depth guide