



KH 5-40

- Combination hammer with 2 functions: hammer drilling and chiselling
- Metabo S-automatic safety clutch: mechanical decoupling of the drive for safe working should the drill stop unexpectedly
- Robust die cast aluminium gear housing for optimum heat dissipation and long service life

| Order no. | 600763500 |
|-------------------------------------|-------------------|
| EAN code | 4007430331724 |
| Max. single blow energy (EP-TA) | 7.1 J |
| Maximum impact rate | 2800 bpm |
| Rated input power | 1100 W |
| Drill-Ø concrete with hammer drills | 40 mm / 1 9/16 " |
| Drill-Ø masonry with core bits | 105 mm / 4 1/8 " |
| No-load speed | 620 rpm |
| Bit retainer | SDS-max |
| Collar diameter | 61 mm / 2.4 " |
| Weight (without power cable) | 7.1 kg / 15.7 lbs |
| Cable length | 4 m / 13 ft |

Scope of delivery

rubber-coated side handle, Drilling depth guide, Lubricant for tool shank end, Plastic carry case