



HK 18 LTX 20

- Versatile cordless glue gun for repairing and fixing at any location. Ready for operation in only 1 minute
- For hot gluing of almost all materials, also heat-sensitive materials thanks to second temperature setting with 130°C
- For glue sticks with Ø 11 mm, also for "low melt" sticks with low processing temperature
- Optimum, fast processing of the glue thanks to constant temperature
- High battery pack performance of up to 13 glue sticks at the highest temperature setting (Li-Power battery pack 18 V/2 Ah)
- Precise, interchangeable nozzle and large, ergonomic feed switch for accurate dosing
- Automatic safety shutdown after 10 minutes of inactivity
- Clean working without dripping by means of anti-drip nozzle
- Safe placing on its side or on the battery pack
- With metaBOX, the intelligent solution for transport and storage
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	600797840
EAN code	4061792246973
Type of battery pack	Li-Power / LiHD
Battery voltage	18 V
Maximum adhesive output	20 g/min / 0.7 oz/min
Processing temperature	200 / 130 °C // 390 / 265 °F
Warm up time	1 min
Glue stick Ø	11 mm / 7/16 "
Weight without battery pack	0.4 kg / 0.9 lbs
Weight with battery pack	0.8 kg / 1.8 lbs

Scope of delivery

Long nozzle Ø 2.8 mm, 5 transparent glue sticks, metaBOX 145, without battery pack, without charger