



KS 55 FS

- Robust circular saw, can be used directly on guide rails from Metabo and also Mafell, Bosch, Festool, Makita, HiKOKI, Hilti and other manufacturers
- Light guide plate made from die cast aluminium
- Grip area with non-slip soft-grip surface
- Clearly visible cutting indicator for precise sawing after initial cut
- 0° position re-adjustable for highest cutting precision
- Extraction possibility by means of connecting an all-purpose vacuum cleaner
- Adjustment of machine without tools for using with the precision guide rail

Order no.	600955500
EAN code	4007430230447
Rated input power	1200 W
Output power	670 W
Maximum cutting depth at 90°	55 mm / 2 5/32 "
Maximum cutting depth at 45°	39 mm / 1 17/32 "
Max. cutting depth with guide rail	50 mm / 1 31/32 "
Saw blade Ø x bore	160 x 20 mm // 6 1/4 x 0.787 "
Swivel range from / to:	0 / + 47 °
No-load speed	5600 rpm
Speed at rated load	4400 rpm
Max. cutting speed	47 m/s / 154 ft/s
Torque	5 Nm / 44 in-lbs
Weight (without power cable)	4 kg / 8.8 lbs
Cable length	4 m / 13 ft

Scope of delivery

Carbide circular saw blade (18 teeth), Parallel guide, Extraction connector, Hexagonal wrench, Plastic carry case