



P 4000 G

- For garden irrigation and groundwater pumping as well as pumping, pumping empty, circulation of clear water
- Maintenance-free capacitor motor
- Overload protection: protects the motor from overheating
- High-quality slip seal system for long service life
- Separate water filling opening for simple operation of the pump
- Water drain plug (removable without tools) for protection in case of frost
- Rubberised feet for low-noise and low-vibration operation
- Ergonomic handle for comfortable transport
- For garden irrigation with 1 to 3 sprinklers

Order no.	600964000
EAN code	4007430240767
Rated input power	1100 W
Maximum delivery rate	4000 l/h / 1057 gal/h
Maximum delivery height	46 m / 151 ft
Maximum pressure	4.6 bar / 66.7 psi
Maximum suction height	8 m / 26 ft
Suction port	1" female thread
Discharge port	1" female thread
Pump housing	Grey cast iron
Protection type IP	IP X4
Drive shaft	Stainless steel
Number of impellers	1
Dimensions	380 x 210 x 290 mm // 14 31/32 x 8 1/4 x 11 13/32 "
Weight	12.2 kg / 26.9 lbs
Cable length	1.5 m / 5 ft

Scope of delivery

Fabric Sealing Tape