



P 4500 Inox

- For garden irrigation and groundwater pumping as well as pumping, pumping empty, circulation of clear water
- Maintenance-free capacitor motor
- Overload protection: protects the motor from overheating
- High-quality slip seal system for long service life
- Durable stainless steel pump housing
- Separate water filling opening for simple operation of the pump
- Water drain plug (removable without tools) for protection in case of frost
- Rubberised feet for low-noise and low-vibration operation
- Ergonomic handle for comfortable transport
- For garden irrigation with 1 to 3 sprinklers

Order no.	600965000
EAN code	4007430240736
Rated input power	1300 W
Maximum delivery rate	4500 l/h / 1189 gal/h
Maximum delivery height	48 m / 157 ft
Maximum pressure	4.8 bar / 70 psi
Maximum suction height	8 m / 26 ft
Suction port	1" female thread
Discharge port	1" female thread
Pump housing	Stainless steel
Protection type IP	IP X4
Drive shaft	Stainless steel
Number of impellers	1
Dimensions	408 x 222 x 303 mm // 16 1/16 x 8 3/4 x 11 15/16 "
Weight	10.6 kg / 23.4 lbs
Cable length	1.5 m / 5 ft

Scope of delivery

Fabric Sealing Tape