



## STEB 65 Quick

- Metabo Quick for changing saw blades without tools
- Top handle with non-slip soft-grip surface
- Variospeed (V) Electronics for working with customised stroke rates for the materials used
- Extraction possibility by means of connecting an all-purpose vacuum cleaner
- Chip blowing function for clear view of cutting line

Order no.	601030000
EAN code	4007430289049
Rated input power	450 W
Output power	230 W
Cutting depth wood	65 mm / 2 3/4 "
Cutting depth NF metal	18 mm / 3/4 "
Cutting depth sheet steel	6 mm / 1/4 "
Swivel range from / to:	- 45 / + 45 °
Pendulum stroke levels	4
Strokes in idle	600 - 3000 rpm
Saw blade stroke	18 mm / 23/32 "
Weight (without power cable)	1.9 kg / 4.2 lbs
Cable length	2.5 m / 10 "

### Scope of delivery

Protective glass, Hexagonal wrench