



PowerMaxx BS 12

- Light compact drill/screwdriver with extremely compact design for versatile use
- The Metabo 12 Volt class - lightweight, yet powerful
- Integrated LED work light with night light function for optimal brightness in the work area
- Handy belt hook and bit holder can be fixed either on the right or left side

Order no.	601036890
EAN code	4061792122741
Battery voltage	12 V
Maximum torque - soft	17 Nm / 150 in-lbs
Maximum torque, hard	40 Nm / 354 in-lbs
Adjustable torque	0.5 - 5 Nm // 4 - 44 in-lbs
Drill Ø steel	10 mm / 3/8 "
Drill-Ø soft wood	18 mm / 23/32 "
No-load speeds	0 - 360 / 0 - 1400 rpm
Chuck capacity	1 - 10 mm // 1/32 - 3/8 "
Weight without battery pack	0.84 kg / 1.9 lbs
Weight with battery pack	1.1 kg / 2.4 lbs

Scope of delivery

Keyless chuck, Belt hook and bit case, without battery pack, without charger