



PowerMaxx BS 12 BL Q

- Brushless drill/screwdriver with optimal power for demanding applications
- The Metabo 12 Volt class - lightweight, yet powerful
- Metabo Quick System: quick change of bit retainer and bits, for flexible working
- Integrated LED work light with night light function for optimal brightness in the work area
- Handy belt hook and bit holder can be fixed either on the right or left side

Order no.	601039890
EAN code	4061792122789
Battery voltage	12 V
Maximum torque - soft	18 Nm / 159 in-lbs
Maximum torque, hard	45 Nm / 398.3 in-lbs
Adjustable torque	0.5 - 5 Nm // 4.4 - 44.3 in-lbs
Drill Ø steel	10 mm / 3/8 "
Drill-Ø soft wood	25 mm / 1 "
No-load speeds	0 - 500 / 0 - 1650 rpm
Chuck capacity	1.5 - 10 mm // 1/16 - 3/8 "
Weight without battery pack	0.84 kg / 1.9 lbs
Weight with battery pack	1.1 kg / 2.4 lbs

Scope of delivery

Quick-change chuck, Belt hook and bit case, without battery pack, without charger