



PowerMaxx SB 12

- Light, compact cordless hammer drill with extremely compact design for versatile use
- The Metabo 12 Volt class - lightweight, yet powerful
- Hammer drill function for drilling in masonry
- Integrated LED work light with night light function for optimal brightness in the work area
- With handy belt hook and bit case which can be fixed either on the right or left side

Order no. EAN code	601076890 4061792122772
Battery voltage	12 V
Maximum torque - soft	17 Nm / 150.5 in-lbs
Maximum torque, hard	40 Nm / 354 in-lbs
Adjustable torque	0.5 - 5 Nm // 4 - 44 in-lbs
Drill-Ø masonry	10 mm / 3/8 "
Drill Ø steel	10 mm / 3/8 "
Drill-Ø soft wood	18 mm / 23/32 "
No-load speed	0 - 360 / 0 - 1400 rpm
Maximum impact rate	21000 bpm
Chuck capacity	1.5 - 10 mm // 1/16 - 3/8 "
Weight without battery pack	0.9 kg / 2 lbs
Weight with battery pack	1.1 kg / 2.4 lbs

Scope of delivery

Keyless chuck, Belt hook and bit case, without battery pack, without charger