



## STE 100 Quick

- Extremely slim jigsaw for perfect handling in any application
- Precise and material-matched sawing due to the variable stroke rate, pendulum stroke and low-lying saw blade guidance with spring support
- Metabo Quick for tool-free saw blade change and with automatic ejection
- Selectable chip blowing function ensures free view of cutting line
- Vario-Tacho-Constamatic (VTC)-Full Wave Electronics for work with materials requiring customised stroke rates, which remain almost constant under load
- Extraction possibility by means of connecting an all-purpose vacuum cleaner
- Non-detachable protective glass that can be pushed down for effective extraction and for protection against flying chips
- Precision guide rail and guiding device available as accessory

<b>Order no.</b>	<b>601100500</b>
<b>EAN code</b>	<b>4007430305114</b>

Rated input power	710 W
Output power	470 W
Cutting depth wood	100 mm / 4 "
Cutting depth NF metal	25 mm / 1 "
Cutting depth sheet steel	10 mm / 3/8 "
Swivel range from / to:	- 45 / + 45 °
Pendulum stroke levels	4
Strokes in idle	1000 - 3100 rpm
Saw blade stroke	22 mm / 7/8 "
Weight (without power cable)	2 kg / 4.5 lbs
Cable length	4 m / 13 ft

### Scope of delivery

Extraction Nozzles, Protective glass, Chip Guard Plates, Jigsaw blade wood, Hexagonal wrench, Plastic carry case