



STE 100 Quick Set with 20 jigsaw blades

- Extremely slim jigsaw for perfect handling in any application
- Precise and material-matched sawing due to the variable stroke rate, pendulum stroke and low-lying saw blade guidance with spring support
- Metabo Quick for tool-free saw blade change and with automatic ejection
- Selectable chip blowing function ensures free view of cutting line
- Vario-Tacho-Constamatic (VTC)-Full Wave Electronics for work with materials requiring customised stroke rates, which remain almost constant under load
- Extraction possibility by means of connecting an all-purpose vacuum cleaner
- Non-detachable protective glass that can be pushed down for effective extraction and for protection against flying chips
- Precision guide rail and guiding device available as accessory

| | |
|-----------|---------------|
| Order no. | 601100900 |
| EAN code | 4007430305121 |

| | |
|------------------------------|-----------------|
| Rated input power | 710 W |
| Output power | 470 W |
| Cutting depth wood | 100 mm / 4 " |
| Cutting depth NF metal | 25 mm / 1 " |
| Cutting depth sheet steel | 10 mm / 3/8 " |
| Swivel range from / to: | - 45 / + 45 ° |
| Pendulum stroke levels | 4 |
| Strokes in idle | 1000 - 3100 rpm |
| Saw blade stroke | 22 mm / 7/8 " |
| Weight (without power cable) | 2 kg / 4.5 lbs |
| Cable length | 4 m / 13 ft |

Scope of delivery

Extraction Nozzles, Protective glass, Chip Guard Plates, 20 Jigsaw blades, Hexagonal wrench, Plastic carry case