



PowerMaxx SSD 12 BL

- Unique Metabo brushless motor for quick work progress and highest efficiency for any application
- Compact cordless impact wrench for tough applications
- The Metabo 12 Volt class - lightweight, yet powerful
- Integrated work light for illumination of the work area
- Robust die cast aluminium gear housing for optimum heat dissipation and durability
- With handy belt hook and bit case which can be fixed either on the right or left side

Order no.	601115890
EAN code	4061792003767
Battery voltage	12 V
Max. screw size	M14
Max. no-load speed	0 - 2500 rpm
Maximum impact rate	4000 bpm
Maximum torque	140 Nm / 105 ft. lbs
Speed/torque levels	2
Bit retainer	Hexagon recess 1/4" (6.35 mm)
Weight without battery pack	0.77 kg / 1.7 lbs
Weight with battery pack	1 kg / 2.2 lbs

Scope of delivery

Belt hook and bit case, without battery pack, without charger