



MT 400 Quick Set for wood

- Indispensable for interior development such as cutting, sanding and scraping of different materials
- Tool holder for maximum compatibility to OIS, Starlock and other accessories
- Metabo Quick tool change system for time-saving, convenient change of accessories
- Fast and powerful thanks to the combination of a large oscillation angle of 3.2° and VTC-Electronics to maintain constant speed even under load
- Extra bright double LED lights for good visibility of the working area
- Slim design and non-slip soft-grip surface for optimised handling
- Extraction possibility by means of connecting an all-purpose vacuum cleaner
- With metaBOX, the intelligent solution for transport and storage

Order no.	601406500
EAN code	4007430317315

Orbital frequency with no load	11000 - 18500 rpm
Rated input power	400 W
Oscillation angle left/right	1.6 °
Bit retainer	Compatible with OIS and Starlock
Base plate, dimensions from corner to corner	93 mm / 3 5/8 "
Weight (without power cable)	1.4 kg / 3.2 lbs

Scope of delivery

Plunge saw blade 32 mm HCS (wood), Segment saw blade 85 mm BiM (wood + metal), Scraping knife, rigid 52 mm HCS, Triangular hook and loop sanding plate 93 mm, 5 Hook and loop sanding sheets 93 mm P 80, 5 Hook and loop sanding sheets 93 mm P 120, Suction Adapter, Multi-adapter, Tool box, metaBOX 145