



## BSA 12-18 LED 2000

- Compact cordless site light with COB-LED for a targeted, true colour illumination, ideal in tight spaces
- Integrated magnets for fast fixing on metal surfaces
- Swivelling hook for suspending the lamp
- Operation with all Li-Power and LiHD slide-on 12 and 18 Volt battery packs
- Battery pack runtime at max. luminosity of 75 min per Ampere hour (Ah), e.g. 5 hours with an LiHD battery pack 18 V / 4 Ah
- Battery pack runtime at max. luminosity of 41 min per Ampere hour (Ah), e.g. 2.8 hours with an LiHD battery pack 12 V / 4 Ah
- Lamp head can be turned through 360° providing almost infinite positions for the lamp
- Stepless dimmer function for optimal light with maximum battery run time
- Clearly visible display of the remaining battery runtime, a flashing light warns before the end of the runtime to avoid dangerous situations in the dark
- Prepared for tripod use (5/8" thread)
- Protected from dust and splash-proof for demanding building site use (IP 54)
- Rubberised stand for secure positioning and gentle contact on delicate surfaces
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: [www.cordless-alliance-systems.com](http://www.cordless-alliance-systems.com)

| Order no.                              | 601504850  |
|--|--|
| EAN code                               | 4061792216150  |
| Battery voltage                        | 12 - 18 V  |
| Max. luminous flux                     | 2000 lm  |
| Max. operation time per battery charge | 12 V Battery pack 4.0 Ah LiHD: 2.7 h / 18 V Battery pack 4.0 Ah LiHD: 5 h / (approx. 75 minutes per Ah at max light output) / (approx. 65 minutes per Ah at max. light output) |
| Weight without battery pack            | 1.2 kg   |
| Weight with battery pack               | 1.6 kg   |

### Scope of delivery

without battery pack, without charger