



BSA 18 LED 4000

- Compact cordless site light with 4000 lumens for extensive and even working light with reduced shadowing
- Integrated magnets for fast fixing on metal surfaces
- Handle and light, compact design for quick change of position and for on the go
- Practical suspension possibilities on lamp base and housing recess
- Battery pack runtime at max. luminosity of 35 min per Ampe-re hour (Ah), e.g. 5.8 hours with an LiHD battery pack 18 V / 10 Ah
- Lamp head can be turned 270° providing almost infinite posi-tions for the lamp
- Stepless dimmer function for optimal light with maximum battery run time
- Clearly visible display of the remaining battery runtime, a flashing light warns before the end of the runtime to avoid dangerous situations in the dark
- Prepared for tripod use (5/8" thread)
- Protected from dust and splash-proof for demanding building site use (IP 54)
- USB port for charging and operating USB devices (max. char-ging current 1 A)
- Rubberised stand for secure positioning and gentle contact on delicate surfaces
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	601505850
EAN code	4061792217782
Max. luminous flux	4000 lm
Max. operation time per batte-ry charge	18V Battery pack 4.0 Ah LiHD: 2.3 h / 18V Batte-ry pack 10.0 Ah LiHD: 6.5 h / (ap-prox. 35 minutes per Ah at max. light output) / (ap-prox. 35 minutes per Ah at max. light output)
Weight without battery pack	1.9 kg
Weight with battery pack	2.5 kg

Scope of delivery

without battery pack, without charger