



BSA 18 LED 10000

- Compact cordless site light with 10,000 lumens for extensive and even working light with reduced shadowing
- Cordless and mains operation possible for continuous operation in the working environment (mains cable can be removed)
- Pure battery pack runtime at max. luminosity of 15 minutes per Ampere hour (Ah), e.g. 2.5 hours with an LiHD battery pack 18 V/10 Ah
- Stepless dimmer function for optimal light with maximum battery run time
- Clearly visible display of the remaining battery runtime, a flashing light warns before the end of the runtime to avoid dangerous situations in the dark
- Prepared for tripod use (5/8" thread)
- Protected from dust and splash-proof for demanding building site use (IP 54)
- USB port for charging and operating USB devices (max. charging current 1 A)
- Rubberised stand for secure positioning and gentle contact on delicate surfaces
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	601506850
EAN code	4061792217829
Max. luminous flux	10000 lm
Max. operation time per battery charge	18V Battery pack 4.0 Ah LiHD: 1 h / 18V Battery pack 10.0 Ah LiHD: 2.5 h / (approx. 15 minutes per Ah at max. light output) / (approx. 15 minutes per Ah at max. light output)
Weight without battery pack	4.1 kg
Weight with battery pack	5.1 kg

Scope of delivery

Removable mains cable (3 m), without battery pack, without charger