



Power 180-5 W OF

- Compact and mobile piston compressor for flexible use both indoors and on construction sites
- Portable assembly compressor – ideal for tackers and nails as well as for splitting pipes
- For single phase alternating current
- Oil-free piston compressor: simple transportation and reduced service requirements
- Instrument panel with easy to read manometer for tank- and working pressure
- Operating pressure can be regulated according to application by means of a pressure reducer and manometer
- Fittings and control elements protected in tubular frames and clearly visible
- Cable winding mechanism
- Convenient pressure switch for good cold starting, complete with relief valve
- Overload protection: protects the motor from overheating
- Rubberised feet for optimum stability

Order no.	601531000
EAN code	4007430244406
Suction rate	160 l/min / 42 gal/h
Filling capacity	90 l/min / 3.2 cfm
Effective delivery volume (at 80% max. pressure)	75 l/min / 2.6 cfm
Maximum pressure	8 bar / 116 psi
Rated input power	1.1 kW / 1.5 HP
Maximum speed	2850 rpm
Tank capacity	5 l / 1.3 gal
Sound pressure level (LpA)	82 dB(A)
Sound power level (LwA)	96 dB(A)
Dimensions	370 x 395 x 286 mm // 1.3 x 1.3 x 1 ft
Weight	16 kg / 35.3 lbs
Cable length	2.4 m / 8 ft

Scope of delivery

Universal quick-action coupling