



Mega 520-200 D

- More powerful and robust V-belt compressor for demanding use
- Belt drive for low speeds and a particularly quiet operation
- For three-phase current
- Working pressure can be regulated according to application by means of a filter pressure reducer with manometer
- Convenient pressure switch for good cold starting, complete with relief valve
- Additional manometer for displaying the tank pressure
- Overload protection: protects the motor from overheating
- Oil-lubricated 2-cylinder piston compressors for high air supply volume
- Rubberised, stable wheels and pull handle for mobile use
- 10 year tank warranty against rust

Order no.	601541000
EAN code	4007430244789
Suction rate	490 l/min / 129 gal/h
Filling capacity	370 l/min / 13.1 cfm
Effective delivery volume (at 80% max. pressure)	320 l/min / 11.3 cfm
Maximum pressure	10 bar / 145 psi
Mains voltage	380 - 415 V
Rated input power	3 kW / 4 HP
Maximum speed	1300 rpm
Tank capacity	200 l / 52.8 gal
Sound pressure level (LpA)	89 dB(A)
Sound power level (LwA)	96 dB(A)
Dimensions	1500 x 450 x 960 mm // 5 x 1.5 x 3.2 ft
Weight	131 kg / 289 lbs
Cable length	1.5 m / 5 ft

Scope of delivery

3 Universal couplings