



DSSW 930-1/2"

- For tightening car wheel bolts, for assembly work and repairs. Universal use
- Practical and lightweight for easy operation even in difficult to reach places
- Ergonomic composite housing: insulated non-slip and low vibration for comfortable work
- Ergonomic forward/reverse switching with convenient one-hand operation
- User-friendly exhaust guide through the handle avoids dust turbulence in the working area
- Torque can be set at 3 levels for different tightening applications
- Durable twin hammer

Order no.	601549000
EAN code	4007430244987

Operating pressure	6.2 bar / 90 psi
Air requirement	9 l/s / 19 cfm
Square holder	1/2"
Maximum torque	650 Nm / 480 ft. lbs
Max. loosening torque	980 Nm / 730 ft. lbs
Weight	1.8 kg / 4 lbs

Scope of delivery

EURO Plug-in nipple 1/4", ARO/Orion Plug-in nipple 1/4", ISO Plug-in nipple 1/4", Hose nozzle 10 mm and hose clamp according to ISO 11148, Oil bottles