



DSSW 1690-3/4"

- For tightening/loosening wheel bolts on cars and commercial vehicles, for assembly work and repairs. Universal use
- Practical and lightweight for easy operation even in difficult to reach places
- Ergonomic composite housing: insulated non-slip and low vibration for comfortable work
- Ergonomic forward/reverse switching with convenient one-hand operation
- User-friendly exhaust guide through the handle avoids dust turbulence in the working area
- Torque can be set at 3 levels for different tightening applications
- Durable twin hammer

Order no.	601550000
EAN code	4007430244994
Operating pressure	6.2 bar / 90 psi
Air requirement	10.5 l/s / 22 cfm
Square holder	3/4"
Maximum torque	1100 Nm / 810 ft. lbs
Max. loosening torque	1690 Nm / 1250 ft. lbs
Weight	3.5 kg / 7.7 lbs

Scope of delivery

EURO Plug-in nipple 3/8", ARO/Orion Plug-in nipple 3/8", ISO Plug-in nipple 3/8", Hose nozzle 10 mm and hose clamp according to ISO 11148, Oil bottles