



DRS 95-1/2"

- Ideally suited for all car applications
- Universal application for all tightening & loosening tasks
- Ergonomic fwd/rev switch
- Rubberised handle for ergonomic and fatigue-free operation
- High-performance planetary gear train for a long service life and optimum transmission of force
- User-friendly, rotating exhaust guide: no dust turbulence in the working area

Order no.	601553000
EAN code	4007430245052
Operating pressure	6.2 bar / 90 psi
Air requirement	450 l/min / 16 cfm
Square holder	1/2"
Speed (RPM)	160 rpm
Max. loosening torque	95 Nm / 841 in-lbs
Weight	1.2 kg / 2.6 lbs

Scope of delivery

EURO Plug-in nipple 1/4", ARO/Orion Plug-in nipple 1/4", ISO Plug-in nipple 1/4", Oil bottles